



Pass and Seymour
Magnetic Latching Relay, 24VAC/24VDC Control
Part No. 1070B



Low Voltage Component, Magnetic Latching Relay, 24VAC/24VDC Control. Reliable field-tested switching circuitry that provide central or local control of lighting loads.

Features & Benefits

Mount in standard 1/2" KO through noise suppressing nylon ring.	Maximum ambient temp: 140: F (60:).
Insulated flame retardant nylon shell.	Prestripped 5-1/2" (140mm) #22 AWG leads for easy wiring.
Split coil design energizes ON coil to close line contacts, and OFF coil to open contacts.	Can be mounted in any position.
Operates on momentary impulse.	Draws .520 mA.
For covering patents, see www.legrand.us/patents .	

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
UPC Number	785007200270	Country Of Origin	Mexico
Application Sector	Commercial	Standard	UL listed

Dimensions

Product Width US	1.176 in	Product Height US	3.156 in
------------------	----------	-------------------	----------

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	20282
------------	-----	-----------------	-------