



Ortronics

Brocade 10G-XFP-ZR Compatible 10GBase-ZR XFP Transceiver (SMF, 1550nm, 80km, LC Duplex, DDM, I-Temp)

Part No. 10G-XFP-ZR-L



10GBase-ZR XFP Compatible Transceiver SMF, 1550nm, 80km, LC Duplex, DDM, I-Temp

Features & Benefits

Guaranteed Compatible

In System tested in over 90 OEM switches, routers and servers.

Industry Leading Lifetime Warranty

For more information by product line, visit our Warranty page.

Full Service Technical Support

Call, chat, email or meet for expert optical connectivity support.

99.98% Reliability Rate

Functionally, optically and environmentally tested to exact specifications.

98% On-Time Delivery Rate

Extensive inventory guarantees same day shipping.

Specifications

General Info

Product Line	Ortronics	Country Of Origin	China
Type	Transceiver		

Technical Information

Fiber Optic Cable Type	Single-Mode	Operating Temperature Min	-40 C
Operating Temperature Max	85 C	Data Transfer Rate	10 Gbps
Connector Type	LC Duplex	Wavelength	1550nm
Form Factor	XFP		