



Ortronics

Telco 10GERTDDXFP Compatible 10GBase-ER XFP Transceiver (SMF, 1550nm, 40km, LC Duplex, DDM, I-Temp)

Part No. 10GERTDDXFP-L



Nokia 3HE00070CB Compatible 1000Base-CWDM SFP Transceiver (SMF, 1490nm, 120km, LC Duplex, DDM, I-Temp)

Features & Benefits

Guaranteed Compatible
In System tested in over 90 OEM switches, routers and servers.

Industry Leading Lifetime Warranty
For more information by product line, visit our Warranty page.

Full Service Technical Support
Call, chat, email or meet for expert optical connectivity support.

99.98% Reliability Rate
Functionally, optically and environmentally tested to exact specifications.

98% On-Time Delivery Rate
Extensive inventory guarantees same day shipping.

Specifications

General Info

Product Line	Ortronics	Country Of Origin	China
Warranty Type	Lifetime	Type	Transceiver

Technical Information

Fiber Optic Cable Type	Single-Mode	Operating Temperature Min	-40 C
Operating Temperature Max	85 C	Data Transfer Rate	10 Gbps
Connector Type	LC Duplex	Wavelength	1550nm