



Pressure Sensitive Door & Canopy Switch 15 Amp 120 Vac, 15 Amp 250 Vac

Features & Benefits

Easily accessible break-off separate or common feed.

Long-life red neon lamp in pilot light rated 1/25 Watt, 125V.

Side wire #12 and #14 AWG.

Two devices fit into the space of one.

Grounding combination devices meet NEC Requirements.

Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

UPC Number	785007120011	Country Of Origin	Mexico
Product Line	Pass & Seymour	Application Sector	Residential/Commercial
Standard	UL Listed		

Technical Information

Number of Poles	Single Pole	Voltage	120 V
Contact Configuration	N-0	Contact Rating	15 Amp, 120/250 VAC
Action	SP	Environmental Conditions	Flammability: UL94 V2
Operating Cycles	30000		