



Pressure Sensitive Door and Canopy Switch 15A 120VAC, 15A 250VAC

Features & Benefits

Easily accessible break-off separate or common feed.

Long-life red neon lamp in pilot light rated 1/25 Watt, 125V.

Side wire #12 and #14 AWG.

Two devices fit into the space of one.

Grounding combination devices meet NEC Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	785007120011
Country Of Origin	Mexico	Features	Pressure Sensitive Switch
Switch Type	Canopy	Number of Switches	1
Application Sector	Commercial, Residential	Wall Plate Included	No
Standard	UL Listed	Warranty Type	1-Year Limited Warranty
Type	Switch		

Dimensions

Product Width US	1.516 in	Product Depth US	1.344 in
Product Height US	4.031 in		

Technical Information

Load Rating	15 A @ 120/250 VAC	Contact Configuration	N-0
Operating Cycles	30000	Connection Location	Side Only
Terminal Accommodation	#14 AWG - #12 AWG	Number of Gangs	1
Throw Type	Single Throw	Amperage	15 A
Number of Poles	Single Pole	Requires Neutral Wire	Yes
Indoor/Outdoor	Indoor	Mounting Type	Wall Box
Wire Connection Type	Wire Terminal	Voltage	120 VAC, 250 VAC
Load Type	CFL, Fluorescent, Halogen, Incandescent, LED, Universal, Xenon	Environmental Conditions	Flammability: UL94 V2