



Pressure Sensitive Door and Canopy Switch 15A 120VAC, 15A 250VAC

## Features & Benefits

Easily accessible break-off separate or common feed.

Long-life red neon lamp in pilot light rated 1/25 Watt, 125V.

Side wire #12 and #14 AWG.

Two devices fit into the space of one.

Grounding combination devices meet NEC Requirements. Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

Product Line	Pass & Seymour	Country Of Origin	Mexico
Application Sector	Residential/Commercial	Standard	UL Listed

### Dimensions

Product Width US	1.516 in	Product Depth US	1.344 in
Product Height US	4.031 in		

### Technical Information

Contact Configuration	N-O	Operating Cycles	30000
Contact Rating	120/250 VAC, 15 Amp	Amperage	15 A

---

Action	SP	Number of Poles	Single Pole
--------	----	-----------------	-------------

---

Voltage	120.0 V	Environmental Conditions	Flammability: UL94 V2
---------	---------	--------------------------	-----------------------

---