

Double Pole, Double Throw Switch, 20 amps, 120/277 volts, Locking.



Features & Benefits

Oversize silver alloy contacts for long life and better heat dissipation.

Fiber terminal insulation barriers standard.

Bodies, covers, and toggles molded of durable nylon.

Locking Switches supplied with one 1498-NT key.

For covering patents, see www.legrand.us/patents.

Side wired terminals accept #14 - #10 AWG copper or copper-clad conductors.

Can be mounted in standard device boxes or in NEMA 1 sheet steel enclosures.

Single Pole-Double Throw and Double Pole-Double Throw.

Normally open.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

Specifications

General Info

Color	Gray	UPC Number	785007122626
Country Of Origin	Mexico	Product Line	Pass & Seymour
Standard	UL Listed		

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	17949
------------	-----	-----------------	-------

Technical Information

Wattage	2 W	Voltage	120 V
---------	-----	---------	-------