



Pass and Seymour  
30A Double Pole, Double Throw Switch, Ivory  
Part No. 1228I

Double-Pole, Double-Throw Switch, 30A, 120/277V.



## Features & Benefits

Oversize silver alloy contacts for long life and better heat dissipation.	Side wired terminals accept #14 - #10 AWG copper or copper-clad conductors.
Fiber terminal insulation barriers standard.	Can be mounted in standard device boxes or in NEMA 1 sheet steel enclosures.
Bodies, covers, and toggles molded of durable nylon.	Single Pole-Double Throw and Double Pole-Double Throw.
Locking Switches supplied with one 1498-NT key.	Normally open.
For covering patents, see <a href="https://www.legrand.us/patents">https://www.legrand.us/patents</a> .	For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, visit <a href="https://www.legrand.us/electrical-wiring-devices/wall-plates">www.legrand.us/electrical-wiring-devices/wall-plates</a> .

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Ivory
Finish	Matte	UPC Number	785007122817
Country Of Origin	Mexico	Features	Durable
Switch Type	Toggle	Number of Switches	1
Application Sector	Commercial, Industrial	Wall Plate Included	No

Standard	UL listed	Warranty Type	1-Year Limited Warranty
Type	Manual Controller		
Dimensions			
Product Width US	1.5 in	Product Depth US	1.469 in
Product Height US	3.281 in		
Listing Agencies / 3rd Party Agencies			
CSA Listed	Yes	cULus Listed	Yes
CSA File Number	17949		
Technical Information			
Load Rating	30 A @ 120/277 VAC	Connection Location	Side Only
Terminal Accommodation	#14 AWG - #10 AWG	Number of Gangs	1
Throw Type	Double Throw	Amperage	30 A
Number of Poles	Double Pole	Requires Neutral Wire	Yes
Indoor/Outdoor	Indoor	Mounting Type	Wall Box
Wire Connection Type	Screw Terminals	Voltage	120 VAC, 277 VAC
Load Type	CFL, Fluorescent, Halogen, Incandescent, LED, Universal, Xenon		