




Pass and Seymour
15A Single Pole, Double Throw Switch, Brown
Part No. 1250



Single-Pole, Double-Throw Switch. 15A, 120/277VAC rating. Tested to 3 Amps, 24Vdc rating.

Features & Benefits

Oversize silver alloy contacts for long life and better heat dissipation.

Side wired terminals accept #14 - #10 AWG copper or copper-clad conductors.

Fiber terminal insulation barriers standard.

Can be mounted in standard device boxes or in NEMA 1 sheet steel enclosures.

Bodies, covers, and toggles molded of durable nylon.

Single Pole-Double Throw and Double Pole-Double Throw.

Locking Switches supplied with one 1498-NT key.

Normally open.

For covering patents, see www.legrand.us/patents.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Specifications

General Info

Product Line	Pass & Seymour	Color	Brown
Finish	Matte	UPC Number	785007125009
Country Of Origin	Mexico	Switch Type	Momentary
Application Sector	Commercial, Residential	Standard	UL Listed
Type	Switch		

Dimensions

Product Width US	1.5 in	Product Depth US	1.469 in
------------------	--------	------------------	----------

Product Height US	3.281 in
-------------------	----------

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus Listed	Yes
------------	-----	--------------	-----

CSA File Number	17949
-----------------	-------

Technical Information

Throw Type	Double Throw	Amperage	15 A
------------	--------------	----------	------

Number of Poles	Single Pole	Wire Size	#14 - #10 AWG
-----------------	-------------	-----------	---------------

Mounting Type	Box	Voltage	120/277 V
---------------	-----	---------	-----------