



Locking Manual Controller, Single-Pole, Double-Throw Switch. 15A, 120/277VAC rating, Tested to 3A, 24VDC rating.

## Features & Benefits

Oversize silver alloy contacts for long life and better heat dissipation.

Fiber terminal insulation barriers standard.

Bodies, covers, and toggles molded of durable nylon.

Locking Switches supplied with one 1498-NT key.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Side wired terminals accept #14 - #10 AWG copper or copper-clad conductors.

Can be mounted in standard device boxes or in NEMA 1 sheet steel enclosures.

Single Pole-Double Throw and Double Pole-Double Throw.

Normally open.

## Specifications

### General Info

Product Line	Wattstopper	Color	Light Almond
Finish	Matte	UPC Number	754182125029
Country Of Origin	Mexico	Application Sector	Commercial, Residential
Type	Manual Controller		

### Dimensions

Product Width US	2.0 in	Product Weight US	0.25 lb
Product Volume US	27.0 cu in	Product Depth US	4.5 in

Product Height US	2.4 in
-------------------	--------

Technical Information

Amperage	15 A	Wire Size	#14 - #10 AWG
----------	------	-----------	---------------

Voltage	120.0 V
---------	---------