



**Wattstopper**  
**Heavy Duty Momentary Toggle Switch White**  
Part No. 1250-W

- Single Pole, Double Throw Switch. 15 Amps, 120/277VAC rating, Brown. Tested to 3 Amps, 24Vdc rating.

## Features & Benefits

---

Oversize silver alloy contacts for long life and better heat dissipation.	Side wired terminals accept #14 - #10 AWG copper or copper-clad conductors.
Fiber terminal insulation barriers standard.	Can be mounted in standard device boxes or in NEMA 1 sheet steel enclosures.
Bodies, covers, and toggles molded of durable nylon.	Single Pole-Double Throw and Double Pole-Double Throw.
Locking Switches supplied with one 1498-NT key.	Normally open.
For covering patents, see <a href="http://www.legrand.us/patents">www.legrand.us/patents</a> .	For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, <a href="#">click here</a> .

## Specifications

---

### General Info

---

Color	White	UPC Number	754182125142
Country Of Origin	China	Product Line	Wattstopper

---