



Pass and Seymour  
Discontinued - 30A Single Pole, Double Throw Switch Brown  
Part No. 1275



Single Pole, Double Throw Switch, 30 amps, 120/277 volts, Brown. 

## Features & Benefits

Oversize silver alloy contacts for long life and better heat dissipation.

Side wired terminals accept #14 - #10 AWG copper or copper-clad conductors.

Fiber terminal insulation barriers standard.

Can be mounted in standard device boxes or in NEMA 1 sheet steel enclosures.

Bodies, covers, and toggles molded of durable nylon.

Single Pole-Double Throw and Double Pole-Double Throw.

Locking Switches supplied with one 1498-NT key.

Normally open.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Brown
UPC Number	785007127508	Country Of Origin	Mexico
Standard	UL Listed		

### Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus Listed	Yes
CSA File Number	17949		

---

Technical Information

---

Amperage	30 A	Wattage	1 W
----------	------	---------	-----

---