



Pass and Seymour  
**15A, 250V Watertight Plug, Black**  
Part No. 14W49BK



Rated watertight for 1,500 psi high-pressure hosedown, Pass and Seymour watertight plugs and connectors feature multiple seals to ensure protection against the environment. Thermoplastic elastomer (TPV) construction stands up to impacts, oils, chemicals, heat and weather.

## Features & Benefits

Thermoplastic elastomer (TPV) construction stands up to impacts, oils, chemicals, heat and weather.

Devices resist high-pressure hose down of 1,500 psi.

Large ribs on body for a superior grip when mating.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

Nickel-plated blades and contacts for long-lasting, superior corrosion resistance.

Color-coded sealing bushings provided for a large range of cord diameters.

All black construction.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Black
Country Of Origin	United States	Application Sector	Commercial
Standard	CSA Listed, FSUL, UL Listed		

### Dimensions

Product Width US	1.85 in	Product Depth US	2.62 in
------------------	---------	------------------	---------

### Technical Information

Phase	Single	Connection	Cable
Number of Wires	3	Amperage	15 A

Number of Poles	Double Pole	Wire Size	18 - 12 AWG
Voltage	250.0 V	Environmental Conditions	Moisture Resistance NEMA 3R (Flip Lid Assemblies/Back Boxes) Flammability UL94V0 (boxes & wiring device interiors) UL94V2 (cover plates) UL94HB (wiring device housings, flip lid seals) Operating Temperature -40°C (without impact) to +60°C continuous UV Resistance All exposed materials are UV stabilized