



Tamper-Resistant Display Receptacle, 15A 125V With Brass Plate and plug.

Features & Benefits

| | |
|--|--|
| Dual mechanical shutter system to help prevent insertions of foreign objects | .032 inch thick brass triple-wipe power contacts for lasting retention |
| Corrosion-resistant plated steel strap is locked in to the face and back body to resist pulling away from the face/body assembly | Auto-ground clip assures positive ground |
| Easily accessed break-off line contact connecting tab for fast and easy split circuit wiring | |

Specifications

General Info

| | | | |
|---------------------|-------------------------|--------------------|------------------|
| Product Line | Pass & Seymour | Color | Brass |
| Finish | Metallic | UPC Number | 785007108767 |
| Country Of Origin | United States | Cover Type | Tamper-Resistant |
| Features | Recessed | Application Sector | Commercial |
| Wall Plate Included | No | Standard | cULus, FEDSPEC |
| Warranty Type | 1-Year Limited Warranty | Type | Outlet |

Listing Agencies / 3rd Party Agencies

| | |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Additional Information

| | |
|----------------|-----|
| RoHS Compliant | Yes |
|----------------|-----|

Technical Information

| | | | |
|---------------------|-----------|-----------------|---|
| Connection Location | Side Only | Number of Wires | 3 |
|---------------------|-----------|-----------------|---|

| | | | |
|-----------------|---|-----------------|-------|
| Number of Gangs | 1 | Number of Poles | 3-Way |
|-----------------|---|-----------------|-------|

| | | | |
|----------------|--------|-------------------------|-------|
| Indoor/Outdoor | Indoor | NEMA Configuration Code | 5-15R |
|----------------|--------|-------------------------|-------|

| | | | |
|---------------|-------------|--------------------|----------|
| Mounting Type | Screw Mount | Box Cover Position | Vertical |
|---------------|-------------|--------------------|----------|

| | | | |
|----------------------|-----------------|---------|---------|
| Wire Connection Type | Screw Terminals | Voltage | 125.0 V |
|----------------------|-----------------|---------|---------|

| | | | |
|--------------------------|---|--|--|
| Environmental Conditions | 85% (relative humidity, non-condensing) | | |
|--------------------------|---|--|--|
