



Pass and Seymour  
**Tamper Resistant Display Receptacle 15A 125V with Brass Plate**  
Part No. 1542TRDR



Tamper-Resistant Display Receptacle, 15A 125V With Brass Plate and plug.

## Features & Benefits

Dual mechanical shutter system to help prevent insertions of foreign objects

.032 inch thick brass triple-wipe power contacts for lasting retention

Auto-ground clip assures positive ground

Backed-out tri-drive steel terminal screws with side wire capability

Two drive screws anchor strap to back body and face where abrupt removal torque is greatest

Corrosion-resistant plated steel strap is locked in to the face and back body to resist pulling away from the face/body assembly

Easily accessed break-off line contact connecting tab for fast and easy split circuit wiring

## Specifications

### General Info

Product Line	Pass & Seymour	UPC Number	785007108767
Country Of Origin	United States	Receptacle Type	Straight Blade
Number of Receptacles	1	Construction	Thermoplastic and Brass
Installation Location	On Floor	Type	Floor Box, Tamper-Resistant

### Listing Agencies / 3rd Party Agencies

cULus Listed Yes

### Technical Information

Is Tamper-Resistant Yes Gangs 1

---

Number of Gangs	1	Current Rating	15 A
Connector Type	Power	Indoor/Outdoor	Indoor
Cable Entry	No in	NEMA Configuration Code	NEMA 5-15R
Mounting Type	Flush	Number of Outlets	1
Voltage	125 VAC		

---