



Conducts an automatic test every three seconds, ensuring it's always ready to protect. If the device fails the test, the indicator light flashes to signal that the GFCI should be replaced. It also has our proven SafeLock<sup>®</sup> Protection feature: if critical components are damaged and protection is lost, power to the receptacle is disconnected. For detailed Tamper-Resistant receptacle information, visit our [Tamper-Resistant Receptacles page](#).

## Features & Benefits

Hospital Grade Tamper Resistant GFCI

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Light Almond
Country Of Origin	China	Application Sector	Residential/Commercial
Standard	cULus, UL Listed, FSUL		

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

### Technical Information

Is Tamper-Resistant	Yes	Interrupt Rating	4 A
Frequency Rating	60 Hz	Trip Range	5±1 mA
Connection	Back and Side Wire	Amperage	15 A
Number of Poles	Double Pole	Voltage	125.0 V
Environmental Conditions	95% Humidity, UL 94 V2		