



Pass and Seymour
radiant 15A Hospital Grade Tamper Resistant Self Test GFCI USB Type CC Outlet Gray
Part No. 1597HGTRUSBCCGRY



Temporarily Unavailable:

Provide superior safety and the convenience of built-in USB charging, with this first-of-its-kind outlet. Perfect for adding modern connectivity anywhere desired, even in the areas of hospital and healthcare facilities where ground fault protection is required. This outlet makes it easy to see and reset electrical trips right where they happen, while also providing two USB connections for keeping phones or tablets charged, no bulky adapter necessary.

Features & Benefits

First outlet of its kind to add USB connection to a GFCI outlet for easier charging, anywhere

Rated for use in hospitals and healthcare facilities, this outlet offers superior durability and reliable ground fault protection. Includes a trip indicator light and reset button on the outlet for easy, accessible troubleshooting

Includes traditional power outlets and two USB Type-C ports for convenient, future-proof charging. Shares 2.0A charging capacity between both ports

Self-tests every three seconds, ensuring continuous ground fault protection for greater safety. Additionally, in case of test failure, the indicator light (red LED) will flash to signal there is an issue and the outlet should be replaced

Equipped with proven SafeLock™ feature which disconnects power to the outlet if any critical components are damaged for added protection

Prevents the insertion of foreign objects while maintaining a discreet, invisible effect with patented, black "invisi-shutter" system. Meets NEC® Tamper-Resistant requirements

Installs quickly thanks to a redesigned side wire cavity for easier access

Can provide ground fault protection to downstream outlets through feed-thru wiring

Specifications

General Info

| | | | |
|-------------------|-------------------------------------|-----------------------|------------------------|
| Color | Gray | UPC Number | 785007377682 |
| Country Of Origin | China | Product Line | Pass & Seymour |
| Finish | Matte | Application Sector | Residential/Commercial |
| Type | Duplex, GFCI, Tamper-Resistant, USB | Number of Receptacles | 2 |
| Warranty Type | 1-Year Limited Warranty | | |

Listing Agencies / 3rd Party Agencies

| | | | |
|-----------------|-------------------------------------|---------------------|---------|
| cULus Listed | Yes | CSA Listed | Yes |
| CSA File Number | CSA C22.2 No. 223, CSA C22.2 No. 42 | cULus ListingNumber | E140596 |

Additional Information

RoHS Compliant Yes

Technical Information

| | | | |
|----------------|--------|----------------------|-----|
| Wattage | 1875 W | Number of Gangs | 1 |
| Voltage | 125 V | Mounting Type | Box |
| Number of USBs | 2 | Is Weather Resistant | No |
| Indoor/Outdoor | Indoor | Is Tamper-Resistant | Yes |
