



Pass and Seymour  
Hospital Grade 15A Duplex Self-Test GFCI Receptacles with SafeLock® Protection, White  
Part No. 1597HGW



Hospital-Grade 15A Self-Test Duplex GFCI

Features & Benefits

Hospital Grade Self-Test GFCI

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	Country Of Origin	China
Number of Receptacles	2	Outlet Type	Commercial, GFCI, Indoor, Self-Test
Application Sector	Residential/Commercial	Standard	cULus, UL Listed, FSUL
Warranty Type	1-Year Limited Warranty	Type	Outlet

Dimensions

Product Width US	1.73 in	Product Depth US	1.03 in
Product Height US	4.2 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Additional Information

---

Product Environmental Profile	Yes
-------------------------------	-----

---

Technical Information

Interrupt Rating	4 A	Frequency Rating	60 Hz
------------------	-----	------------------	-------

---

Trip Range	5±1 mA	Amperage	15 A
------------	--------	----------	------

---

Number of Poles	Double Pole	Indoor/Outdoor	Indoor
-----------------	-------------	----------------	--------

---

Voltage	125.0 V
---------	---------

---