



Pass and Seymour  
Isolated Ground Tamper-Resistant 15A Duplex Self-Test GFCI Receptacles with SafeLock® Protection, Orange  
Part No. 1597IGTRO



Conducts an automatic test every three seconds, ensuring it fts always ready to protect. If the device fails the test, the indicator light flashes to signal that the GFCI should be replaced. It also has our proven SafeLockandtrade- Protection fiveature: if critical components are damaged and protection is lost, power to the receptacle is disconnected.For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

## Features & Benefits

Hospital Grade Tamper Resistant GFCI

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Orange
UPC Number	785007048612	Country Of Origin	China
Number of Receptacles	2	Features	Isolated Ground, Self-Test
Outlet Type	GFCI, Tamper-Resistant	Application Sector	Commercial, Multi-Dwelling Unit, Residential
Wall Plate Included	Yes	Standard	cULus, UL Listed, FSUL
Warranty Type	1-Year Limited Warranty		

### Dimensions

Product Width US	1.73 in	Product Depth US	1.0303 in
Product Height US	4.2003 in		

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

### Additional Information

---

Product Environmental Profile    Yes

---

Technical Information

Is Tamper-Resistant	Yes	Connection Location	Back and Side
Frequency Rating	60 Hz	Number of Wires	3
Amperage	15 A	Number of Poles	Double Pole
Indoor/Outdoor	Indoor	NEMA Configuration Code	5-15R
Wire Connection Type	Internal Pressure Plates, Screw Terminals	Voltage	125.0 V
Environmental Conditions	95% Humidity, UL 94 V2		

---