



radiant Collection
radiant® 15A Tamper-Resistant Self-Test GFCI USB Type-AA Outlet, Brown
Part No. 1597TRUSBAA



Temporarily Unavailable:

Enjoy superior safety and the convenience of built-in USB charging, in a first-of-its-kind outlet! Perfect for adding modern connectivity anywhere, including areas of the home where ground fault protection is required (kitchens, bathrooms, laundry rooms, etc). This outlet makes it easy to see and reset electrical trips right where they happen, while also providing two USB connections for keeping phones or tablets charged, no bulky adapter required.

Features & Benefits

- First outlet of its kind to add USB connection to a GFCI outlet for easier charging, anywhere
- Provides reliable ground fault protection with a trip indicator light and reset button on the outlet for easy, accessible troubleshooting
- Includes traditional power outlets and two USB Type-A ports for convenient charging. Shares 2.0A charging capacity between both ports
- Self-tests every three seconds, ensuring continuous ground fault protection for greater safety. Additionally, in case of test failure, the indicator light (red LED) will flash to signal there is an issue and the outlet should be replaced
- Equipped with proven SafeLock™ feature which disconnects power to the outlet if any critical components are damaged for added protection
- Protect children using a patented “invisi-shutter” system to prevent the insertion of foreign objects while maintaining a discreet, invisible effect. Meets NEC® Tamper-Resistant requirements
- Installs quickly thanks to a redesigned side wire cavity for easier access
- Can provide ground fault protection to downstream outlets through feed-thru wiring

Specifications

General Info

Color	Brown	UPC Number	785007309881
Country Of Origin	China	Product Line	Pass & Seymour
Finish	Matte	Application Sector	Residential/Commercial
Type	GFCI	Number of Receptacles	2
Warranty Type	1-Year Limited Warranty	Construction	Polycarbonate

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes	CSA Listed	Yes
--------------	-----	------------	-----

CSA File Number	CSA AC22.2 No.223, CSA C22.2 No.42	cULus ListingNumber	E140596
-----------------	---------------------------------------	---------------------	---------

Additional Information

RoHS Conformant	Yes
-----------------	-----

Technical Information

Wattage	1875 W	Number of Poles	Double Pole
---------	--------	-----------------	-------------

Number of Gangs	1	Voltage	125 V
-----------------	---	---------	-------

Mounting Type	Box	Number of USBs	2
---------------	-----	----------------	---

Is Weather Resistant	No	Indoor/Outdoor	Indoor
----------------------	----	----------------	--------

Is Tamper-Resistant	Yes
---------------------	-----
