



radiant Collection  
radiant® GFCI USB Outlet, Type A, 15A, Tamper-Resistant, Nickel  
Part No. 1597TRUSBAANIC4



Enjoy superior safety and the convenience of built-in USB charging, in a first-of-its-kind outlet! Perfect for adding modern connectivity anywhere, including areas of the home where ground fault protection is required (kitchens, bathrooms, laundry rooms, etc). This outlet makes it easy to see and reset electrical trips right where they happen, while also providing two USB connections for keeping phones or tablets charged, no bulky adapter required. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

## Features & Benefits

First outlet of its kind to add USB connection to a GFCI outlet for easier charging, anywhere

Includes traditional power outlets and two USB Type-A ports for convenient charging. Shares 2.0A charging capacity between both ports

Equipped with proven SafeLock™ feature which disconnects power to the outlet if any critical components are damaged for added protection

Installs quickly thanks to a redesigned side wire cavity for easier access

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Provides reliable ground fault protection with a trip indicator light and reset button on the outlet for easy, accessible troubleshooting

Self-tests every three seconds, ensuring continuous ground fault protection for greater safety. Additionally, in case of test failure, the indicator light (red LED) will flash to signal there is an issue and the outlet should be replaced

Protect children using a patented “invisi-shutter” system to prevent the insertion of foreign objects while maintaining a discreet, invisible effect. Meets NEC® Tamper-Resistant requirements

Can provide ground fault protection to downstream outlets through feed-thru wiring

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Nickel
Finish	Matte	UPC Number	785007374933
Country Of Origin	China	Number of Receptacles	2
Construction	Polycarbonate	Features	USB-A Charging

Outlet Type	GFCI, Self-Test, Tamper-Resistant, USB-Charging		Application Sector	Commercial, Multi-Dwelling Unit, Residential
Wall Plate Included	No		Warranty Type	1-Year Limited Warranty
Type	Outlet			
Dimensions				
Product Width US	1.73 in		Product Depth US	1.03 in
Product Height US	4.2 in			
Technical Information				
Is Tamper-Resistant	Yes		Connection Location	Back and Side
USB Amperage	2 A		Number of USBs	2
Number of Wires	3		Number of Gangs	1
Amperage	15 A		Number of Poles	Double Pole
Is Weather Resistant	No		Indoor/Outdoor	Indoor
Wattage	1875 W		NEMA Configuration Code	5-15R
Mounting Type	Box		Wire Connection Type	Internal Pressure Plates, Screw Terminals
Voltage	125.0 V			