



## Legrand

radiant® 15A Tamper-Resistant Self-Test GFCI USB Type-AA Outlet, Nickel, 4-Pack

Part No. 1597TRUSBAANIC4



Enjoy superior safety and the convenience of built-in USB charging, in a first-of-its-kind outlet! Perfect for adding modern connectivity anywhere, including areas of the home where ground fault protection is required (kitchens, bathrooms, laundry rooms, etc). This outlet makes it easy to see and reset electrical trips right where they happen, while also providing two USB connections for keeping phones or tablets charged, no bulky adapter required.

### Features & Benefits

First outlet of its kind to add USB connection to a GFCI outlet for easier charging, anywhere

Provides reliable ground fault protection with a trip indicator light and reset button on the outlet for easy, accessible troubleshooting

Includes traditional power outlets and two USB Type-A ports for convenient charging. Shares 2.0A charging capacity between both ports

Self-tests every three seconds, ensuring continuous ground fault protection for greater safety. Additionally, in case of test failure, the indicator light (red LED) will flash to signal there is an issue and the outlet should be replaced

Equipped with proven SafeLock™ feature which disconnects power to the outlet if any critical components are damaged for added protection

Protect children using a patented "invisi-shutter" system to prevent the insertion of foreign objects while maintaining a discreet, invisible effect. Meets NEC® Tamper-Resistant requirements

Installs quickly thanks to a redesigned side wire cavity for easier access

Can provide ground fault protection to downstream outlets through feed-thru wiring

### Specifications

#### General Info

Color Nickel

UPC Number 785007374933

Country Of Origin China

Product Line Pass & Seymour

Finish Matte

Application Sector Residential/Commercial

Type GFCI

Warranty Type 1 Year from Day of Sale

Construction Polycarbonate

#### Listing Agencies / 3rd Party Agencies

CSA Listed Yes

CSA File Number CSA C22.2 No. 223, C22.2 No. 51

---

**Technical Information**

---

**Wattage** 1875 W

---

**Number of Poles** Double Pole

---

**Voltage** 125 V

---

**Is Weather Resistant** No

---

**Indoor/Outdoor** Indoor

---

**Is Tamper-Resistant** Yes

---