



## radiant Collection

**Discontinued - radiant® 15A Tamper Resistant Self Test GFCI USB Type CC Outlet**

Part No. 1597TRUSBCCDB



Enjoy superior safety and the convenience of built-in USB charging, in a first-of-its-kind outlet! Perfect for adding modern connectivity anywhere, including areas of the home where ground fault protection is required (kitchens, bathrooms, laundry rooms, etc). This outlet makes it easy to see and reset electrical trips right where they happen, while also providing two USB connections for keeping phones or tablets charged, no bulky adapter required.

## Features & Benefits

First outlet of its kind to add USB connection to a GFCI outlet for easier charging, anywhere

Includes traditional power outlets and two USB Type-A ports for convenient charging. Shares 2.0A charging capacity between both ports

Equipped with proven SafeLock™ feature which disconnects power to the outlet if any critical components are damaged for added protection

Installs quickly thanks to a redesigned side wire cavity for easier access.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Provides reliable ground fault protection with a trip indicator light and reset button on the outlet for easy, accessible troubleshooting

Self-tests every three seconds, ensuring continuous ground fault protection for greater safety. Additionally, in case of test failure, the indicator light (red LED) will flash to signal there is an issue and the outlet should be replaced

Protect children using a patented “invisi-shutter” system to prevent the insertion of foreign objects while maintaining a discreet, invisible effect. Meets NEC® Tamper-Resistant requirements

Can provide ground fault protection to downstream outlets through feed-thru wiring.

## Specifications

### General Info

Product Line	Pass & Seymour	Replaced by Part Number	1597TRUSBCCDBC4
Color	Dark Bronze	Finish	Matte
Country Of Origin	China	Number of Receptacles	2
Features	USB-C Charging	Outlet Type	GFCI, Indoor, Residential, Self-Test, Tamper-Resistant, USB-Charging

---

Warranty Type	1-Year Limited Warranty	Type	Outlet
---------------	-------------------------	------	--------

---

### Dimensions

---

Product Width US	1.74 in	Product Depth US	2.15 in
------------------	---------	------------------	---------

---

Product Height US	4.19 in
-------------------	---------

---

### Listing Agencies / 3rd Party Agencies

---

CSA Listed	Yes	cULus ListingNumber	E140596
------------	-----	---------------------	---------

---

cULus Listed	Yes	CSA File Number	CSA C22.2 No. 223, CSA C22.2 No. 75
--------------	-----	-----------------	-------------------------------------

---

### Additional Information

---

RoHS Conformant	Yes
-----------------	-----

---

### Technical Information

---

USB Amperage	2.1 A	Number of USBs	2
--------------	-------	----------------	---

---

Number of Gangs	1	Amperage	15 A
-----------------	---	----------	------

---

Number of Poles	Double Pole	Indoor/Outdoor	Indoor
-----------------	-------------	----------------	--------

---

Wattage	1875 W	Mounting Type	Box
---------	--------	---------------	-----

---

Voltage	125.0 V
---------	---------

---