



radiant Collection
radiant® 15A Tamper-Resistant Outdoor Self Test GFCI USB Type C/C Outlet, White
Part No. 1597TRWRUSBCCW



Enjoy superior safety and the convenience of built-in USB charging, in a first-of-its-kind outlet! Perfect for adding modern connectivity anywhere, including areas of the home where ground fault protection is required. Also including tamper and weather resistance, this model was designed for use on decks, patios, pool areas, and other outdoor spaces. Easily see and reset electrical trips right where they happen, while gaining two USB connections for keeping phones or tablets charged, no bulky adapter necessary.

Features & Benefits

First outlet of its kind to add USB connection to a GFCI outlet for easier charging, anywhere	Provides reliable ground fault protection for use in outdoor spaces, including patios, decks and pool areas. Includes a trip indicator light and reset button on the outlet for easy, accessible troubleshooting
Includes traditional power outlets and two USB Type-C ports for convenient, future-proof charging. Shares 2.0A charging capacity between both ports	Self-tests every three seconds, ensuring continuous ground fault protection for greater safety. Additionally, in case of test failure, the indicator light (red LED) will flash to signal there is an issue and the outlet should be replaced
Equipped with proven SafeLock™ feature which disconnects power to the outlet if any critical components are damaged for added protection	Designed with weather-resistance for use in outdoor locations such as decks, patios and pool areas. *Must be installed in weatherproof enclosure per NEC requirements
Protect children using a patented “invisi-shutter” system to prevent the insertion of foreign objects while maintaining a discreet, invisible effect. Meets NEC® Tamper-Resistant requirements	Installs quickly thanks to a redesigned side wire cavity for easier access. Can provide ground fault protection to downstream outlets through feed-thru wiring

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	Country Of Origin	China
Number of Receptacles	2	Features	USB-C Charging
Outlet Type	GFCI, Outdoor, Residential, Self-Test, Tamper-Resistant, USB-Charging	Application Sector	Residential/Commercial

Warranty Type	1-Year Limited Warranty	Type	Duplex, GFCI, Tamper-Resistant, USB, Weather-Resistant
---------------	-------------------------	------	--

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus ListingNumber	E140596
cULus Listed	Yes	CSA File Number	CSA C22.2 No. 223, CSA C22.2 No. 42

Additional Information

RoHS Conformant	Yes
-----------------	-----

Technical Information

Is Tamper-Resistant	Yes	USB Amperage	2.1 A
Number of USBs	2	Number of Gangs	1
Amperage	15 A	Is Weather Resistant	Yes
Indoor/Outdoor	Outdoor	Wattage	1875 W
Mounting Type	Box	Voltage	125 V