



Legrand

15/10A, 125/250V Watertight Straight Blade Connector, Yellow
Part No. 15W07



Rated watertight for 1,500 psi high-pressure hosedown, P&S plugs and connectors feature multiple seals to ensure protection against the environment. Constructed of a sturdy rubber body, which makes them impact- and chemical-resistant, they have nickel-plated blades and contacts for superior corrosion resistance.

Features & Benefits

Rubber body construction stands up to impacts, oils, chemicals, heat and weather.

Terminal screws backed-out, ready-to-wire, saving time and money.

Compression-type cord grip provides watertight seal and 205 lb. pull out strength.

Quick-drive assembly screws allow for fast installation to save time and money.

Floating blades allow self-alignment with contacts for a firm, even electrical connection.

Nickel-plated blades and contacts for long-lasting, superior corrosion resistance.

Multiple ring seals between plug and connector ensures protection from water and contaminants.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Color Yellow

UPC Number 785007033717

Countries Of Origin United States

Product Line Pass & Seymour

Application Sector Commercial

Standard CSA Listed, FSUL, UL Listed

Technical Information

Number of Poles 3-Way

Voltage 125 V

Connection Cable

Phase Single

Wire Size 18AWG - 12AWG

Number of Wires 3

Environmental Conditions Moisture Resistance NEMA 3R (Flip Lid Assemblies/Back Boxes) Flammability UL94V0 (boxes & wiring device interiors) UL94V2 (cover plates) UL94HB (wiring device housings, flip lid seals) Operating Temperature -40°C (without impact) to +60°C continuous UV Resistance All exposed materials are UV stabilized
