



Pass and Seymour
20A, 250V Watertight Connector, Yellow
Part No. 15W48



Rated watertight for 1,500 psi high-pressure hosedown, Pass and Seymour plugs and connectors feature multiple seals to ensure protection against the environment. Constructed of a sturdy rubber body, which makes them impact- and chemical-resistant, they have nickel-plated blades and contacts for superior corrosion resistance.

Features & Benefits

Thermoplastic elastomer (TPV) construction stands up to impacts, oils, chemicals, heat and weather.

Multi-point sealing system provides environmental protection of NEMA 4, 4X, 6, 6P, & IP67 rated.

Color-coded sealing bushings provided for large range of cord diameters

For covering patents, see www.legrand.us/patents.

Nickel-plated blades and contacts for long-lasting, superior corrosion resistance.

Devices resist high-pressure hose down of 1,500 psi.

Large ribs on body for a superior grip when mating.

Specifications

General Info

Product Line	Pass & Seymour	Color	Yellow
Country Of Origin	United States	Application Sector	Commercial
Standard	UL 498		

Dimensions

Product Height US	1.85 in	Product Length US	4.03 in
-------------------	---------	-------------------	---------

Technical Information

Number of Wires	3	Amperage	30 A
Number of Poles	Double Pole	Wire Size	14 - 12 AWG
Voltage	125.0 V		

