



Pass and Seymour
15A, 250V Watertight Straight Blade Connector, Black
Part No. 15W49BK



Rated watertight for 1,500 psi high-pressure hosedown, Pass and Seymour watertight plugs and connectors feature multiple seals to ensure protection against the environment. Thermoplastic elastomer (TPV) construction stands up to impacts, oils, chemicals, heat and weather.

Features & Benefits

Thermoplastic elastomer (TPV) construction stands up to impacts, oils, chemicals, heat and weather.

Multi-point sealing system provides environmental protection of NEMA 4, 4X, 6, 6P, & IP67 rated.

Color-coded sealing bushings provided for large range of cord diameters

For covering patents, see www.legrand.us/patents.

Nickel-Plated blades and contacts for long lasting, superior corrosion resistance.

Devices resist high-pressure hose down of 1,500 psi.

Large ribs on body for a superior grip when mating.

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
UPC Number	785007040845	Country Of Origin	United States
Application Sector	Commercial	Standard	CSA Listed, FSUL, UL Listed

Dimensions

Product Width US	1.85 in	Product Length US	2.62 in
------------------	---------	-------------------	---------

Technical Information

Phase	Single	Connection	Cable
-------	--------	------------	-------

Number of Wires	3	Amperage	15 A
Number of Poles	Double Pole	Wire Size	18 - 12 AWG
Environmental Conditions	Moisture Resistance NEMA 3R (Flip Lid Assemblies/Back Boxes) Flammability UL94V0 (boxes & wiring device interiors) UL94V2 (cover plates) UL94HB (wiring device housings, flip lid seals) Operating Temperature -40°C (without impact) to +60°C continuous UV Resistance All exposed materials are UV stabilized		