



19.75"W x 38.25"H x 25.00"D

## Features & Benefits

Swing-EZ Wall Racks offer flexibility  
The 25" deep unit gives the flexibility of mounting equipment where space is a premium and a full size rack cannot be used for small offices.

12-24 threaded EIA hole pattern  
Standards compliant to mount numerous types of 19" panels and equipment.

Reinforcement pan attached to bottom of Swing-EZ  
Sturdy and holds equipment up to 150lbs.

Self squaring assembly  
No additional tools required

Front swing gate with latch pins and bolts on both sides:

Allows you to open swing gate either left or right and easy access to rear of panels and equipment.

Side panels fold flat for shipping  
Unfold for easy on site assembly.

Base includes 3" feed through holes  
Allows cable delivery from bottom of rack.

•Includes 12-24 mounting screws  
Do not have to purchase as separate item

## Specifications

### General Info

Product Line	Ortronics	Color	Black
UPC Number	662875580997	Country Of Origin	United States

### Additional Information

RoHS Conformant	Yes	Product Environmental Profile	Yes
-----------------	-----	-------------------------------	-----