



Extreme 1G-SFP-CWDM-1590 Compatible 1000Base-CWDM SFP Transceiver (SMF, 1590nm, 80km, LC Duplex, DDM, I-Temp)

Features & Benefits

- Guaranteed Compatible: In System tested in over 90 OEM switches, routers and servers.
- 99.98% Reliability Rate: Functionally, optically and environmentally tested to exact specifications.
- Industry Leading Lifetime Warranty: For more information by product line, visit our Warranty page.
- 98% On-Time Delivery Rate: Extensive inventory guarantees same day shipping.
- Full Service Technical Support: Call, chat, email or meet for expert optical connectivity support.

Specifications

General Info			
Product Line	Ortronics	Country Of Origin	China
Warranty Type	Lifetime	Type	Transceiver
Dimensions			
Product Width US	13.9 mm	Product Depth US	58.4 mm
Product Height US	8.5 mm		
Technical Information			
Fiber Optic Cable Type	Single-Mode	Operating Temperature Min	-40 C
Operating Temperature Max	85 C	Connector Type	LC Duplex
Form Factor	SFP		