


Legrand keyed LC fiber solutions provide a simple and convenient way to physically prevent the user from making an unauthorized connection by blocking access to specific optical ports, whether they are at a workstation outlet or in a telecommunications room or data center. This is particularly important for government, finance, military and other facilities where multiple networks having different security level access requirements may be co-located.



Features & Benefits

A factory-cleaved 900um fiber stub ensures ease of use and optimal performance

The solution to managing multiple networks with reduced risks

LC SECURE products feature twelve color-coded, keyed designs to limit improper connections networks.

Internal keying feature prevents tampering

50/125 μm and 9/125 μm laser-optimized fiber types available

1.6 in boot protects the splice for easy cable management

LC Keyed cadapters prevent improper connection of separate networks with common access points

Each LC secure adapter will mate only with same-color LC secure connector

High quality 1.25 mm zirconia ferrules used

Specifications

General Info

Type Connector

Technical Information

Fiber Size 9/125 Temperature Rating -40 to +75°C

Service Life < 0.2dB typical change,500 matings