




Ortronics
Infinium Keyed LC Splice-On Connector (SOC) For 900 Micron Fiber, 9/125 Single-Mode OS2 50 Pack Yellow
Part No. 205KKF9SD-09-C



Legrand keyed LC fiber solutions provide a simple and convenient way to physically prevent the user from making an unauthorized connection by blocking access to specific optical ports, whether they are at a workstation outlet or in a telecommunications room or data center. This is particularly important for government, finance, military and other facilities where multiple networks having different security level access requirements may be co-located.

Features & Benefits

12 color/key configurations available

LC Keyed cadapters prevent improper connection of separate networks with common access points

High quality 1.25 mm zirconia ferrules used

High quality 1.25 mm zirconia ferrules used

The solution to managing multiple networks with reduced risks

50/125 microns and 9/125 microns laser-optimized fiber types available

Each LC secure adapter will mate only with same-color LC secure connector

Internal keying feature prevents tampering

1.6 in boot protects the splice for easy cable management

Specifications

General Info

| | | | |
|-------------------|---------------|------------|--------------|
| Product Line | Ortronics | UPC Number | 662875033912 |
| Country Of Origin | United States | Type | Connector |

Dimensions

| | | | |
|-------------------|----------|------------------|---------|
| Product Width US | 0.236 in | Product Depth US | 3.65 in |
| Product Height US | 0.409 in | | |

Technical Information

| | | | |
|--------------|-------------------------------------|--------------------|--------------|
| Service Life | < 0.2dB typical change, 500 matings | Temperature Rating | -40° - 75° C |
| Fiber Size | 9/125 | | |