



Infinium Splice-On connectors by Legrand® enable fast field terminations while meeting or exceeding industry standards for performance. The entire splice is concealed and protected within the strain relief boot and the UV Cure Protection sleeve cures in seconds, reducing the variables that cause critical errors during installation, so you can finish the job quickly and efficiently.

Legrand 3.0mm Splice-On Connectors have a unique boot that allows the entire splice to be concealed and protected. The addition of an extended brass crimp sleeve provides extra protection to the splice and utilizes the Kevlar for maximized pull strength.

## Features & Benefits

### Better Insertion Loss & Return Loss Performance:

Support high-bandwidth/high-speed transmission to 25G, 40G and 100G applications

Available in LC, SC and ST, Single-Mode or Multimode  
Multiple connector types available

### UV Cure Protection Sleeves

Strain relief boot protects the splice point

### 3mm Version

Brass crimp to protect splice

### Fiber endface types

Endfaces available in PC, APC and UPC

Factory-cleaved, pre-polished 900-micron fiber stub  
Provides a quicker termination

900-micron boot conceals and protects the splice  
Enables better cable management

### 3mm Version

3mm boot protects splice for easy cable management

### 3mm Version

Tubing insert to accommodate 1.6/2.0/3.0 cordage

## Specifications

### General Info

Product Line	Ortronics	UPC Number	662875849063
Country Of Origin	United States		