



Infinium Splice-On connectors by Legrand® enable fast field terminations while meeting or exceeding industry standards for performance. The entire splice is concealed and protected within the strain relief boot and the UV Cure Protection sleeve cures in seconds, reducing the variables that cause critical errors during installation, so you can finish the job quickly and efficiently.

Legrand 3.0mm Splice-On Connectors have a unique boot that allows the entire splice to be concealed and protected. The addition of an extended brass crimp sleeve provides extra protection to the splice and utilizes the Kevlar for maximized pull strength.

Features & Benefits

Better Insertion Loss & Return Loss Performance:
Support high-bandwidth/high-speed transmission to 25G, 40G and 100G applications

Available in LC, SC and ST, Single-Mode or Multimode
Multiple connector types available

UV Cure Protection Sleeves
Strain relief boot protects the splice point

3mm Version
Brass crimp to protect splice

Fiber endface types
Endfaces available in PC, APC and UPC

Factory-cleaved, pre-polished 900-micron fiber stub
Provides a quicker termination

900-micron boot conceals and protects the splice
Enables better cable management

3mm Version
3mm boot protects splice for easy cable management

3mm Version
Tubing insert to accommodate 1.6/2.0/3.0 cordage

Specifications

General Info

Product Line	Ortronics	UPC Number	662875915348
Country Of Origin	United States		