



- Conducts an automatic test every three seconds, ensuring it's always ready to protect. If the device fails the test, the indicator light flashes to signal that the GFCI should be replaced. It also has our proven SafeLock® Protection—if critical components are damaged and ground fault protection is lost, power to the receptacle is disconnected. Visual LED power identification of receptacles to ensure proper functionality for necessary loads. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

Features & Benefits

Power Indicating Amber LED flashes if the device needs to be replaced	Hospital Grade GFCI specially designed and tested for rigorous healthcare applications
Tamper-Resistant automatic shutter system prevents insertion. Black shutters essentially “disappear” into the background for an invisible effect preferred by end users	The indicator light flashes if the device fails the self-test, signalling that the GFCI should be replaced
Two back-wire holes per termination add wiring flexibility, eliminate pigtailling and save box space	High-impact-resistant, thermoplastic construction for superior strength and durability
Ground terminal back-wire for fast installation	Auto-ground clip assures a positive ground to metal box
FSUL Listed (Federal Specification WC596)	

Specifications

General Info

Color	Gray	UPC Number	785007289879
Country Of Origin	China	Product Line	Pass & Seymour
Finish	Matte	Type	GFCI, Tamper-Resistant, Duplex, USB
Number of Receptacles	2	Warranty Type	1-Year Limited Warranty

Additional Information

RoHS Conformant	Yes
-----------------	-----

Technical Information

Number of Gangs	1	Voltage	125 V
Mounting Type	Box	Is Weather Resistant	No
Indoor/Outdoor	Indoor	Is Tamper-Resistant	Yes
