



Temporarily Unavailable:

Provide superior safety and the convenience of built-in USB charging, with this first-of-its-kind outlet. Perfect for adding modern connectivity anywhere desired, even in the areas of hospital and healthcare facilities where ground fault protection is required. This outlet makes it easy to see and reset electrical trips right where they happen, while also providing two USB connections for keeping phones or tablets charged, no bulky adapter necessary.

Features & Benefits

<p>First outlet of its kind to add USB connection to a GFCI outlet for easier charging, anywhere</p>	<p>Rated for use in hospitals and healthcare facilities, this outlet offers superior durability and reliable ground fault protection. Includes a trip indicator light and reset button on the outlet for easy, accessible troubleshooting</p>
<p>Includes traditional power outlets, as well as one USB Type-A and one USB Type-C port for convenient charging. Shares 2.0A charging capacity between both ports</p>	<p>Self-tests every three seconds, ensuring continuous ground fault protection for greater safety. Additionally, in case of test failure, the indicator light (red LED) will flash to signal there is an issue and the outlet should be replaced</p>
<p>Equipped with proven SafeLock™ feature which disconnects power to the outlet if any critical components are damaged for added protection</p>	<p>Prevents the insertion of foreign objects while maintaining a discreet, invisible effect with patented, black "invisi-shutter" system. Meets NEC® Tamper-Resistant requirements</p>
<p>Installs quickly thanks to a redesigned side wire cavity for easier access</p>	<p>Can provide ground fault protection to downstream outlets through feed-thru wiring</p>

Specifications

General Info

Color	Black	UPC Number	785007377583
Country Of Origin	China	Product Line	Pass & Seymour
Finish	Matte	Application Sector	Residential/Commercial
Type	GFCI, Tamper-Resistant, Duplex, USB	Number of Receptacles	2
Warranty Type	1-Year Limited Warranty		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes	CSA Listed	Yes
CSA File Number	CSA C22.2 No. 223, CSA C22.2 No. 42	cULus ListingNumber	E140596

Additional Information

RoHS Compliant Yes

Technical Information

Wattage	1875 W	Number of Gangs	1
Voltage	125 V	Mounting Type	Box
Number of USBs	2	Is Weather Resistant	No
Indoor/Outdoor	Indoor	Is Tamper-Resistant	Yes
