



radiant Collection  
radiant® Hospital Grade Tamper-Resistant 20A Duplex Self-Test GFCI Receptacles with SafeLock® Protection, USB Type A/C Outlet, Red  
Part No. 2097HGTRUSBACRED



Provide superior safety and the convenience of built-in USB charging, with this first-of-its-kind outlet. Perfect for adding modern connectivity anywhere desired, even in the areas of hospital and healthcare facilities where ground fault protection is required. This outlet makes it easy to see and reset electrical trips right where they happen, while also providing two USB connections for keeping phones or tablets charged, no bulky adapter necessary. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

## Features & Benefits

First outlet of its kind to add USB connection to a GFCI outlet for easier charging, anywhere	Rated for use in hospitals and healthcare facilities, this outlet offers superior durability and reliable ground fault protection. Includes a trip indicator light and reset button on the outlet for easy, accessible troubleshooting
Includes traditional power outlets, as well as one USB Type-A and one USB Type-C port for convenient charging. Shares 2.0A charging capacity between both ports	Self-tests every three seconds, ensuring continuous ground fault protection for greater safety. Additionally, in case of test failure, the indicator light (red LED) will flash to signal there is an issue and the outlet should be replaced
Equipped with proven SafeLock™ feature which disconnects power to the outlet if any critical components are damaged for added protection	Prevents the insertion of foreign objects while maintaining a discreet, invisible effect with patented, black "invisi-shutter" system. Meets NEC® Tamper-Resistant requirements
Installs quickly thanks to a redesigned side wire cavity for easier access	Can provide ground fault protection to downstream outlets through feed-thru wiring
Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.	

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Red
Finish	Matte	Country Of Origin	China
Number of Receptacles	2	Features	USB-A Charging, USB-C Charging
Outlet Type	GFCI, Indoor, Residential, Self-Test, Tamper-Resistant, USB-Charging	Application Sector	Residential/Commercial
Warranty Type	1-Year Limited Warranty	Type	Outlet

### Dimensions

Product Width US	1.73 in	Product Depth US	1.03 in
Product Height US	4.2 in		

### Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus ListingNumber	E140596
cULus Listed	Yes	CSA File Number	CSA C22.2 No. 223, CSA C22.2 No. 42

### Additional Information

RoHS Conformant	Yes
-----------------	-----

### Technical Information

Is Tamper-Resistant	Yes	USB Amperage	2.1 A
Number of USBs	2	Number of Gangs	1
Amperage	20 A	Number of Poles	Double Pole
Is Weather Resistant	No	Indoor/Outdoor	Indoor
Wattage	1875 W	Mounting Type	Box
Voltage	125.0 V		