



radiant Collection
radiant® 20A Duplex Self-Test GFCI Receptacles with SafeLock® Protection, Red
Part No. 2097RED



GFCI receptacles from the radiant® Collection self-test automatically every three seconds to ensure reliable protection from shock due to ground fault occurrences. Meeting National Electrical Code requirements for ground fault protection, GFCI receptacles make it easier to recognize and fix trips right where they happen – no more confusion at the breaker box. 20A outlets are ideal for use with larger appliances, as well as to meet regional requirements (Chicago, Canada). GFCI protection is required by code in bathrooms, kitchens, garages, basements, outdoor areas, and for any other outlets found within six feet of a sink or water source. GFCI outlets should always be used when replacing existing GFCI outlets during renovation. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately. Spec-Grade devices are engineered to meet federal specifications for use in commercial installations.

Features & Benefits

Protects against shock caused by ground-fault occurrences. Unlike breaker alternatives, GFCI receptacles make it easier to fix trips with a reset button right on the device

Equipped with proven SafeLock protection feature: if critical components are damaged and protection is lost, power to the outlet is disconnected

Replaces any standard receptacle with ease, in as little as 10 minutes

More color options available to fit any style, including finishes to match current hardware and lighting trends

Conducts an industry-leading automatic self-test every 3 seconds. If the device ever fails, the indicator light flashes to signal it should be replaced

Extends GFCI protection to "downstream" outlets when used with feed-thru wiring configuration. Note: Will cut power to face and downstream outlets if wired incorrectly

Features durable, high-impact resistant thermoplastic construction

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection

Specifications

General Info

Product Line	Pass & Seymour	Color	Red
Country Of Origin	China	Number of Receptacles	2
Outlet Type	GFCI, Indoor, Self-Test	Application Sector	Residential/Commercial
Standard	cULus, UL Listed, FSUL	Warranty Type	1-Year Limited Warranty

Dimensions

Product Width US	1.73 in	Product Depth US	1.03 in
Product Height US	4.2 in		

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

Additional Information

Product Environmental Profile Yes

Technical Information

Interrupt Rating	4 A	Frequency Rating	60 Hz
------------------	-----	------------------	-------

Trip Range	5±1 mA	Connection	Back and Side Wire
------------	--------	------------	--------------------

Number of Gangs	1	Amperage	20 A
-----------------	---	----------	------

Mounting Type	Box	Voltage	125.0 V
---------------	-----	---------	---------

Environmental Conditions	95% Humidity, UL 94 V2		
--------------------------	------------------------	--	--
