



GFCI receptacles from the radiant® Collection self-test automatically every three seconds to ensure reliable protection from shock due to ground fault occurrences. Meeting National Electrical Code requirements for ground fault protection, GFCI receptacles make it easier to recognize and fix trips right where they happen – no more confusion at the breaker box. 20A outlets are ideal for use with larger appliances and in commercial settings, as well as to meet regional requirements (Chicago, Canada). GFCI protection is required by code in bathrooms, kitchens, garages, basements, outdoor areas, and for any other outlets found within six feet of a sink or water source. GFCI outlets should always be used when replacing existing GFCI outlets during renovation. Spec-Grade devices are engineered to meet federal specifications for use in commercial installations.

Features & Benefits

| | |
|--|--|
| Alarm rated at 60 db at 10 feet | One-piece, brass, triple-wipe power contacts for lasting retention |
| Conducts an automatic test every three seconds, ensuring it's always ready to protect. If the device fails the test, the trip indicator light (red LED) flashes to signal that the GFCI should be replaced | Equipped with proven SafeLock protection feature: if critical components are damaged and protection is lost, power to the receptacle is disconnected |
| Feed-thru wiring configuration allows GFCI to protect downstream receptacles | Prevents line-load reversal miswire: no power to the face or downstream receptacles if wired incorrectly |
| Mounting screws are shipped captive in the device and wall plate for easier installation | Dual-direction test and reset button colors match the device face |
| Thinner than competitors' GFCI Receptacles: leaves more room for wires in the box | |

Specifications

General Info

| | | | |
|--------------------|--|-----------------------|-----------------------------------|
| Product Line | Pass & Seymour | Color | White |
| Finish | Matte | UPC Number | 785007048285 |
| Country Of Origin | China | Number of Receptacles | 2 |
| Features | Audible Alarm, Self-Test | Outlet Type | GFCI, Self-Test, Tamper-Resistant |
| Application Sector | Commercial, Multi-Dwelling Unit, Residential | Wall Plate Included | Yes |
| Standard | cULus, UL Listed, FSUL | Warranty Type | 1-Year Limited Warranty |

Dimensions

| | | | |
|-------------------|---------|------------------|---------|
| Product Width US | 1.73 in | Product Depth US | 1.03 in |
| Product Height US | 4.2 in | | |

Listing Agencies / 3rd Party Agencies

| | |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Additional Information

| | |
|-------------------------------|-----|
| Product Environmental Profile | Yes |
|-------------------------------|-----|

Technical Information

| | | | |
|-------------------------|-------------|----------------------|--|
| Is Tamper-Resistant | Yes | Connection Location | Back and Side |
| Number of Wires | 3 | Amperage | 20 A |
| Number of Poles | Double Pole | Indoor/Outdoor | Indoor |
| NEMA Configuration Code | 5-20R | Wire Connection Type | Internal Pressure Plates, Screw Terminals |
| Voltage | 125.0 V | | |