



## Features & Benefits

- First outlet of its kind to add USB connection to a GFCI outlet for easier charging, anywhere
- Provides reliable ground fault protection with a trip indicator light and reset button on the outlet for easy, accessible troubleshooting
- Includes traditional power outlets and two USB Type-A ports for convenient charging. Shares 2.0A charging capacity between both ports
- Self-tests every three seconds, ensuring continuous ground fault protection for greater safety. Additionally, in case of test failure, the indicator light (red LED) will flash to signal there is an issue and the outlet should be replaced
- Equipped with proven SafeLock™ feature which disconnects power to the outlet if any critical components are damaged for added protection
- Protect children using a patented "invisi-shutter" system to prevent the insertion of foreign objects while maintaining a discreet, invisible effect. Meets NEC® Tamper-Resistant requirements
- Installs quickly thanks to a redesigned side wire cavity for easier access
- Can provide ground fault protection to downstream outlets through feed-thru wiring

## Specifications

### General Info

|                   |                |                       |  |
|-------------------|----------------|-----------------------|--|
| Product Line      | Pass & Seymour | Color                 | White  |
| Finish            | Matte          | UPC Number            | 785007374551   |
| Country Of Origin | China          | Number of Receptacles | 2  |
| Features          | USB-A Charging | Outlet Type           | Residential, Indoor, GFCI, Tamper-Resistant, Self-Test, USB-Charging |
| Type              | Outlet         |                       |  |

### Listing Agencies / 3rd Party Agencies

|                               |             |                          |                                     |
|-------------------------------|-------------|--------------------------|-------------------------------------|
| CSA Listed                    | Yes         | cULus ListingNumber      | E140596                             |
| cULus Listed                  | Yes         | CSA File Number          | CSA C22.2 No. 223, CSA C22.2 No. 83 |
| <b>Additional Information</b> |             |                          |                                     |
| RoHS Conformant               | Yes         | Prop 65 Warning Required | No                                  |
| <b>Technical Information</b>  |             |                          |                                     |
| USB Amperage                  | 2.1 A       | Number of USBs           | 2                                   |
| Number of Gangs               | 1           | Amperage                 | 20 A                                |
| Number of Poles               | Double Pole | Indoor/Outdoor           | Indoor                              |
| NEMA Configuration Code       | 5-20R       | Mounting Type            | Box                                 |
| Voltage                       | 125 VAC     | Environmental Conditions | 95% Humidity, UL 94 V2              |