



## radiant Collection

Discontinued | radiant® 20A Tamper Resistant Self Test GFCI USB Type A/C Outlet, Nickel | Sub 2097TRUSBACNIC4  
Part No. 2097TRUSBACNI



Enjoy superior safety and the convenience of built-in USB charging, in a first-of-its-kind outlet! Perfect for adding modern connectivity anywhere, including areas of the home where ground fault protection is required (kitchens, bathrooms, laundry rooms, etc). This outlet makes it easy to see and reset electrical trips right where they happen, while also providing two USB connections for keeping phones or tablets charged, no bulky adapter required.

### Features & Benefits

First outlet of its kind to add USB connection to a GFCI outlet for easier charging, anywhere

Provides reliable ground fault protection with a trip indicator light and reset button on the outlet for easy, accessible troubleshooting

Includes traditional power outlets and two USB Type-A ports for convenient charging. Shares 2.0A charging capacity between both ports

Self-tests every three seconds, ensuring continuous ground fault protection for greater safety. Additionally, in case of test failure, the indicator light (red LED) will flash to signal there is an issue and the outlet should be replaced

Equipped with proven SafeLock™ feature which disconnects power to the outlet if any critical components are damaged for added protection

Protect children using a patented "invisi-shutter" system to prevent the insertion of foreign objects while maintaining a discreet, invisible effect. Meets NEC® Tamper-Resistant requirements

Installs quickly thanks to a redesigned side wire cavity for easier access

### Specifications

#### General Info

Product Line	Pass & Seymour	Color	Nickel
Finish	Metallic	UPC Number	785007374711
Country Of Origin	China	Number of Receptacles	2

#### Dimensions

Product Width US	1.73 in	Product Volume US	15.67 cu in
Product Depth US	2.15 in	Product Height US	4.2 in

#### Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus ListingNumber	E140596
cULus Listed	Yes	CSA File Number	CSA C22.2 No. 223, CSA C22.2 No. 99

#### Additional Information

RoHS Conformant	Yes
-----------------	-----

---

## Technical Information

---

Number of USBs	2	Number of Gangs	1
Wattage	1875 W	Mounting Type	Box
Voltage	125 V		

---