



Temporarily Unavailable:

Enjoy superior safety and the convenience of built-in USB charging, in a first-of-its-kind outlet! Perfect for adding modern connectivity anywhere, including areas of the home where ground fault protection is required (kitchens, bathrooms, laundry rooms, etc). This outlet makes it easy to see and reset electrical trips right where they happen, while also providing two USB connections for keeping phones or tablets charged, no bulky adapter required.

## Features & Benefits

First outlet of its kind to add USB connection to a GFCI outlet for easier charging, anywhere	Provides reliable ground fault protection with a trip indicator light and reset button on the outlet for easy, accessible troubleshooting
Includes traditional power outlets and two USB Type-A ports for convenient charging. Shares 2.0A charging capacity between both ports	Self-tests every three seconds, ensuring continuous ground fault protection for greater safety. Additionally, in case of test failure, the indicator light (red LED) will flash to signal there is an issue and the outlet should be replaced
Equipped with proven SafeLock™ feature which disconnects power to the outlet if any critical components are damaged for added protection	Protect children using a patented "invisi-shutter" system to prevent the insertion of foreign objects while maintaining a discreet, invisible effect. Meets NEC® Tamper-Resistant requirements
Installs quickly thanks to a redesigned side wire cavity for easier access	Can provide ground fault protection to downstream outlets through feed-thru wiring

## Specifications

### General Info

Color	Brown	UPC Number	785007374735
Country Of Origin	China	Product Line	Pass & Seymour
Finish	Matte	Number of Receptacles	2
Warranty Type	1-Year Limited Warranty		

### Technical Information

Wattage	1875 W	Number of Gangs	1
Voltage	125 V	Mounting Type	Box

---

Number of USBs

2

---