



Temporarily Unavailable:

Enjoy superior safety and the convenience of built-in USB charging, in a first-of-its-kind outlet! Perfect for adding modern connectivity anywhere, including areas of the home where ground fault protection is required (kitchens, bathrooms, laundry rooms, etc). This outlet makes it easy to see and reset electrical trips right where they happen, while also providing two USB connections for keeping phones or tablets charged, no bulky adapter required.

Features & Benefits

First outlet of its kind to add USB connection to a GFCI outlet for easier charging, anywhere	Provides reliable ground fault protection for use in outdoor spaces, including patios, decks and pool areas. Includes a trip indicator light and reset button on the outlet for easy, accessible troubleshooting
Includes traditional power outlets and two USB Type-C ports for convenient, future-proof charging. Shares 2.0A charging capacity between both ports	Self-tests every three seconds, ensuring continuous ground fault protection for greater safety. Additionally, in case of test failure, the indicator light (red LED) will flash to signal there is an issue and the outlet should be replaced
Equipped with proven SafeLock™ feature which disconnects power to the outlet if any critical components are damaged for added protection	Designed with weather-resistance for use in outdoor locations such as decks, patios and pool areas. *Must be installed in weatherproof enclosure per NEC requirements
Protect children using a patented “invisi-shutter” system to prevent the insertion of foreign objects while maintaining a discreet, invisible effect. Meets NEC® Tamper-Resistant requirements	Installs quickly thanks to a redesigned side wire cavity for easier access. Can provide ground fault protection to downstream outlets through feed-thru wiring

Specifications

General Info

Color	Black	UPC Number	785007377972
Country Of Origin	China	Product Line	Pass & Seymour
Finish	Matte	Application Sector	Residential/Commercial
Type	GFCI, Duplex, Tamper-Resistant, USB, Weather-Resistant	Number of Receptacles	2
Warranty Type	1-Year Limited Warranty		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes	CSA Listed	Yes
CSA File Number	CSA C22.2 No. 223, CSA C22.2 No. 42	cULus ListingNumber	E140596

Additional Information

RoHS Conformant Yes

Technical Information

Wattage	1875 W	Number of Gangs	1
Voltage	125 V	Mounting Type	Box
Number of USBs	2	Is Weather Resistant	Yes
Indoor/Outdoor	Outdoor	Is Tamper-Resistant	Yes
