



GFCI receptacles from the radiant® Collection self-test automatically every three seconds to ensure reliable protection from shock due to ground fault occurrences. Meeting National Electrical Code requirements for ground fault protection, GFCI receptacles make it easier to recognize and fix trips right where they happen – no more confusion at the breaker box. 20A outlets are ideal for use with larger appliances, as well as to meet regional requirements (Chicago, Canada). GFCI protection is required by code in bathrooms, kitchens, garages, basements, outdoor areas, and for any other outlets found within six feet of a sink or water source. GFCI outlets should always be used when replacing existing GFCI outlets during renovation. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately. Spec-Grade devices are engineered to meet federal specifications for use in commercial installations.

Features & Benefits

Part of the radiant: collection	Conducts an automatic test every three seconds, ensuring it's always ready to protect. If the device fails the test, the trip indicator light (red LED) flashes to signal that the GFCI should be replaced
Thinner than competitors' GFCI Receptacles: leaves more room for wires in Feed-thru wiring configuration allows GFCI to protect downstream receptacles the box	
Prevents line-load reversal miswire: no power to the face or downstream receptacles if wired incorrectly	Side or internal screw-pressure-plate back wire with #10-#14 AWG solid or stranded copper wire and two back wire holes per terminal
Mounting screws are shipped captive in the device and wall plate for easier installation	Dual-direction test and reset button colors match the device face
Supplied with matching TP wall plate	10kA short circuit rating
20 Amp feed-thru capacity	

Specifications

General Info

Color	Yellow	UPC Number	785007198089
Country Of Origin	China	Product Line	Pass & Seymour
Number of Receptacles	2	Warranty Type	1-Year Limited Warranty

Dimensions

Product Width US	1.73 in	Product Height US	4.2 in
------------------	---------	-------------------	--------

Product Depth US	1.03 in
------------------	---------

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Number of Gangs	1	Voltage	125 V
-----------------	---	---------	-------

Mounting Type	Box
---------------	-----
