



Wiremold  
**25DTP-E10 - 25DTP Series Steel Tele-Power Pole (Ivory)**  
Part No. 25DTP-E10



Two sections of a two-compartment (power and communication) pole (5'4" (1.626m) base + 5' (1.524m) extender) assembles to form a 10' 4" (3.148m) pole. Nominal material thickness .040" (1.0mm). Ivory or gray boot base. Factory wired with fed-spec general grade 20A 125V duplex style receptacles. An 8" (203mm) cover at top front (power side) of pole is removable for making power wiring connections. KOs provided in removable cover for RJ11/RJ45 and modular furniture communication connectors. Mounting hardware, entrance end plate and two ceiling trim plates furnished.

## Features & Benefits

Add power receptacles or devices to existing modular Tele-Power Poles. Includes one receptacle mounting bracket. Face diameter of single receptacle: 1.38" - 1.40" (35mm - 36mm).

## Specifications

### General Info

Product Line	Wiremold	Color	Ivory
UPC Number	786776172539	Country Of Origin	United States
Product Series	Steel Tele-Power	Application Sector	Commercial
Standard	cULus Listed, Multioutlet Assemblies: File E15191, E178348	Type	Pole

### Dimensions

Product Width US	2.83 in	Product Weight US	22.0 lb
Product Height US	125.0 in		

### Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E15191	cULus Listed	Yes
---------------------	--------	--------------	-----

### Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information			
-----------------------	--	--	--

Cutout	A/V, Data, Keystone, Receptacle	Number of Channels	2
--------	---------------------------------	--------------------	---