



Pass and Seymour Specification Grade Decorator Switch, Ivory Part No. 2622I



Double Pole, Back and Side Wire, Decorator Switch, 20 amps, 120/277 volts, Brown.

Features & Benefits

Impact-resistant polycarb back body and frame.

Unique single rocking butterfly contact provides long term consistent performance with significantly fewer moving parts.

Terminals made of high conductivity brass and serrated for maximum wire gripping.

Integral auto-ground clip for positive ground to metal boxes.

All terminal screws backed out, ready-to-install.

Cushioned thermoplastic paddle assures smooth, quiet, long term operation.

Internal screw-pressure-plate back and side wire capability for easy installation with #14 - #10 stranded or solid copper/copper clad wire.

Silver alloy contacts integrally formed to the butterfly actuator assures reliable performance.

Tri-drive ground, terminal, and mounting screws.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

| | | | |
|--------------------|------------|--------------|----------------|
| Color | Ivory | UPC Number | 785007539431 |
| Country Of Origin | Mexico | Product Line | Pass & Seymour |
| Application Sector | Industrial | Standard | UL 20 |

Listing Agencies / 3rd Party Agencies

| | | | |
|-----------------|-------|---------------------|--------|
| cULus Listed | Yes | CSA Listed | Yes |
| CSA File Number | 17446 | cULus ListingNumber | 140597 |

Technical Information

| | | | |
|----------------|-------------------|---------|-------|
| Wattage | 2 W | Voltage | 120 V |
| Contact Rating | 20amp, 120/277vac | | |