



Specification Grade Decorator Switch 3-way, Back and Side-Wire,
Decorator Switch, 20A, 347V

Features & Benefits

Impact-resistant polycarb back body and frame.	Cushioned thermoplastic paddle assures smooth, quiet, long term operation.
Unique single rocking butterfly contact provides long term consistent performance with significantly fewer moving parts.	Internal screw-pressure-plate back and side wire capability for easy installation with #14 - #10 stranded or solid copper/copper clad wire.
Terminals made of high conductivity brass and serrated for maximum wire gripping.	Silver alloy contacts integrally formed to the butterfly actuator assures reliable performance.
Integral auto-ground clip for positive ground to metal boxes.	Tri-drive ground, terminal, and mounting screws.
All terminal screws backed out, ready-to-install.	For covering patents, see

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
Country Of Origin	Mexico		

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus Listed	Yes
CSA File Number	17446		

Technical Information

Amperage	20 A
----------	------
