



Four-Way, Back and Side Wire, Decorator Switch, 20 amps, 120/277 volts, Brown.

## Features & Benefits

Impact-resistant polycarb back body and frame.

Unique single rocking butterfly contact provides long term consistent performance with significantly fewer moving parts.

Terminals made of high conductivity brass and serrated for maximum wire gripping.

Integral auto-ground clip for positive ground to metal boxes.

All terminal screws backed out, ready-to-install.

Cushioned thermoplastic paddle assures smooth, quiet, long term operation.

Internal screw-pressure-plate back and side wire capability for easy installation with #14 - #10 stranded or solid copper/copper clad wire.

Silver alloy contacts integrally formed to the butterfly actuator assures reliable performance.

Tri-drive ground, terminal, and mounting screws.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

UPC Number	785007539660	Country Of Origin	Mexico
------------	--------------	-------------------	--------

Product Line	Pass & Seymour	Application Sector	Industrial
--------------	----------------	--------------------	------------

Standard	UL 20
----------	-------

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes	CSA Listed	Yes
--------------	-----	------------	-----

CSA File Number	17446	cULus ListingNumber	140597
-----------------	-------	---------------------	--------

---

## Technical Information

---

Wattage	4 W	Number of Poles	4-Way
Voltage	120 V	Contact Rating	20amp, 120/277vac

---