



Pass and Seymour
Decorator 15A Half-Controlled Plug Load Duplex Receptacle, Brown
Part No. 26252CH



This durable, dependable Plug Load receptacle is designed to help you meet ASHRAE energy standards. The controlled marking printed on the tough nylon face is both NEMA-approved and compliant with the National Electrical Code.

Features & Benefits

NEMA approved controlled receptacle marking pad printed on the face of receptacle for superior abrasion resistance.

CH versions feature a factory broken split circuit tab allowing you to control half of the receptacle.

Can be used to control loads using the Wattstopper DLM system and other building control systems.

Corrosion-resistant, plated steel strap locked into assembly to prohibit strap from bending away from body.

One-piece, brass, triple-wipe power contacts for lasting retention.

Heavy-duty compact design for easier installation and long lasting performance.

Impact-resistant nylon face.

Terminal compartments isolated from each other for positive conductor containment.

Side and internal screw-pressure-plate back wire accepts #14 - #10 AWG solid or stranded wire.

All devices fit standard #26 opening wall plate.

Tri-drive terminal and mounting screws.

Auto-ground clip assures positive ground.

For covering patents, see www.legrand.us/patents.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Specifications

General Info

Product Line	Pass & Seymour	Color	Brown
UPC Number	785007032741	Country Of Origin	Mexico
Standard	FEDSPEC		

Dimensions

Product Width US	1.322 in	Product Depth US	0.78 in
------------------	----------	------------------	---------

Product Height US	2.635 in
-------------------	----------

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Amperage	15 A
----------	------
