



Pass and Seymour
DECOR DUP RECP 20A 125V BL
Part No. 26352BL



Heavy-Duty Decorator Spec Grade Duplex Receptacle Back and Side Wire 20A 125V

Features & Benefits

Corrosion-resistant, plated steel strap locked into assembly to prohibit strap from bending away from body.

Heavy-duty compact design for easier installation and long lasting performance.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

Impact-resistant nylon face.

Terminal compartments isolated from each other for positive conductor containment.

All devices fit standard #26 opening wall plate.

Tri-drive terminal and mounting screws.

Auto-ground clip assures positive ground.

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Specifications

General Info

Product Line	Pass & Seymour	Color	Blue
Country Of Origin	Mexico		

Dimensions

Product Width US	1.322 in	Product Depth US	0.78 in
Product Height US	2.635 in	Product Length US	1.0E-4 in

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Amperage	20 A
----------	------