



Pass and Seymour
20A 125V Dual-Controlled Plug Load Decorator Duplex Receptacle, Brown
Part No. 26352CD



This durable, dependable Plug Load receptacle is designed to help you meet ASHRAE energy standards. The controlled marking printed on the tough nylon face is both NEMA-approved and compliant with the National Electrical Code.

Features & Benefits

- NEMA approved controlled receptacle marking pad printed on the face of receptacle for superior abrasion resistance.

Corrosion-resistant, plated steel strap locked into assembly to prohibit strap from bending away from body.

Heavy-duty compact design for easier installation and long lasting performance.

Side and internal screw-pressure-plate back wire accepts #14 - #10 AWG solid or stranded wire.
- Can be used to control loads using the Wattstopper DLM system and other building control systems.

One-piece, brass, triple-wipe power contacts for lasting retention.

Terminal compartments isolated from each other for positive conductor containment.

All devices fit standard #26 opening wall plate.

Specifications

General Info

Product Line	Pass & Seymour	Color	Brown
Country Of Origin	Mexico	Number of Receptacles	2
Outlet Type	Commercial, Energy Saving On/Off, Indoor	Warranty Type	1-Year Limited Warranty
Type	Outlet		

Dimensions

Product Width US	1.322 in	Product Depth US	0.78 in
Product Height US	2.635 in		

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

Technical Information

Amperage	20 A	Number of Poles	Double Pole
Indoor/Outdoor	Indoor	Voltage	125.0 V
